

## SERIES 75

### “TR POLYURETHANE” TRANSPALLET ROLLERS, STEEL CENTRE



#### Roller description

“TR” polyurethane transpallet roller, hardness 95 +/- 3 Shore A, excellent rolling resistance and elasticity, good resistance to wear and to tearing. Weldless steel centre.

#### Hub

The housing is obtained by moulding and turning and contains ball bearings series Z. The hub is available also without bearings.

**Diameters:** 80-85 mm

**Carrying capacities:** 650-1000 daN

### Fittings with swivel and fixed brackets



#### Electro-welded brackets type EE MHD

Max. carrying capacity 900 daN – available diameters 80-250 mm  
Top plate fastening. Adjustable rear-locking brake systems

### Uses

#### Environments

The series is suitable for use in industrial environments for carrying medium-heavy loads, including with mixed outdoor-indoor use. Can be used at speeds of up to 16 km/h; possibility of using for mechanised towing.  
*Usage temperatures:* from -20 °C to +80 °C

#### Floors



#### Handling

