


FILO OVALE / OVAL WIRE / OVAL DRAHT / FIL OVALE

ESEMPIO D'ORDINE / ORDERING EXAMPLE / BESTELLBEISPIEL / EXAMPLE DE COMMANDE: (25) HGO 19 - 051
CONSEGNA DA MAGAZZINO / DELIVERY FROM STOCK / LIEFERUNG AB LAGER / DISPONIBLE SUR STOCK

D _H	D _d	L ₀	N. di catalogo Catalogue No. Bestellnummer N° de catalogue	R	A		B		C		D	
					15% L ₀		20% L ₀		30% L ₀		f _b	
mm	mm	mm		N / mm	N	mm	N	mm	N	mm	N	mm
9.5	4.7	25	HGO 10 - 025	22.5	86	3.8	113	5.0	169	7.5	207	9.2
		32	HGO 10 - 032	18.6	89	4.8	119	6.4	179	9.6	225	12.1
		38	HGO 10 - 038	15.9	91	5.7	121	7.6	181	11.4	210	13.2
		44	HGO 10 - 044	13.7	90	6.6	121	8.8	181	13.2	207	15.1
		51	HGO 10 - 051	11.8	91	7.7	120	10.2	180	15.3	230	19.5
		64	HGO 10 - 064	8.8	84	9.6	113	12.8	169	19.2	192	21.8
		76	HGO 10 - 076	6.4	73	11.4	97	15.2	146	22.8	179	27.9
		305	HGO 10 - 305	1.7	78	45.8	104	61.0	156	91.5	216	127.2
13	7	25	HGO 13 - 025	37.3	142	3.8	187	5.0	280	7.5	366	9.8
		32	HGO 13 - 032	32.5	156	4.8	208	6.4	312	9.6	442	13.6
		38	HGO 13 - 038	28.4	162	5.7	216	7.6	324	11.4	415	14.6
		44	HGO 13 - 044	24.5	162	6.6	216	8.8	323	13.2	443	18.1
		51	HGO 13 - 051	18.6	143	7.7	190	10.2	285	15.3	415	22.3
		64	HGO 13 - 064	15.7	151	9.6	201	12.8	301	19.2	429	27.3
		76	HGO 13 - 076	13.7	156	11.4	208	15.2	312	22.8	453	33.1
		305	HGO 13 - 305	3.1	142	45.8	189	61.0	284	91.5	433	139.7
16	8.7	25	HGO 16 - 025	78.2	297	3.8	391	5.0	587	7.5	657	8.4
		32	HGO 16 - 032	59.8	287	4.8	383	6.4	574	9.6	628	10.5
		38	HGO 16 - 038	51.0	291	5.7	388	7.6	581	11.4	694	13.6
		44	HGO 16 - 044	43.1	284	6.6	379	8.8	569	13.2	685	15.9
		51	HGO 16 - 051	38.2	294	7.7	390	10.2	584	15.3	722	18.9
		64	HGO 16 - 064	31.4	301	9.6	402	12.8	603	19.2	782	24.9
		76	HGO 16 - 076	24.5	279	11.4	372	15.2	559	22.8	715	29.2
		305	HGO 16 - 305	5.7	261	45.8	348	61.0	522	91.5	591	103.6
19.5	9.5	25	HGO 19 - 025	181.4	689	3.8	907	5.0	1361	7.5	1542	8.5
		32	HGO 19 - 032	137.3	659	4.8	879	6.4	1318	9.6	1510	11.0
		38	HGO 19 - 038	107.9	615	5.7	820	7.6	1230	11.4	1370	12.7
		44	HGO 19 - 044	94.1	621	6.6	828	8.8	1242	13.2	1430	15.2
		51	HGO 19 - 051	78.5	604	7.7	801	10.2	1201	15.3	1397	17.8
		64	HGO 19 - 064	65.0	624	9.6	832	12.8	1248	19.2	1489	22.9
		76	HGO 19 - 076	56.9	649	11.4	865	15.2	1297	22.8	1582	27.8
		89	HGO 19 - 089	47.1	631	13.4	838	17.8	1258	26.7	1512	32.1
		102	HGO 19 - 102	41.2	630	15.3	840	20.4	1261	30.6	1529	37.1
		115	HGO 19 - 115	36.3	628	17.3	835	23.0	1252	34.5	1561	43.0
		127	HGO 19 - 127	32.4	619	19.1	823	25.4	1234	38.1	1516	46.8
		305	HGO 19 - 305	14.7	673	45.8	897	61.0	1345	91.5	1695	115.3

Note: 1 N = 0,102 Kg (force)



D _H	D _d	L ₀	N. di catalogo Catalogue No. Bestellnummer N° de catalogue	R	A		B		C		D	
					15% L ₀		20% L ₀		30% L ₀		f _b	
mm	mm	mm		N / mm	N	mm	N	mm	N	mm	N	mm
25.5	13	25	HGO 26 - 025	333.4	1267	3.8	1667	5.0	2501	7.5	2567	7.7
		32	HGO 26 - 032	257.4	1236	4.8	1647	6.4	2471	9.6	2728	10.6
		38	HGO 26 - 038	210.8	1202	5.7	1602	7.6	2403	11.4	2698	12.8
		44	HGO 26 - 044	176.5	1165	6.6	1553	8.8	2330	13.2	2683	15.2
		51	HGO 26 - 051	148.1	1140	7.7	1511	10.2	2266	15.3	2621	17.7
		64	HGO 26 - 064	119.6	1148	9.6	1531	12.8	2296	19.2	2739	22.9
		76	HGO 26 - 076	100.0	1140	11.4	1520	15.2	2280	22.8	2750	27.5
		89	HGO 26 - 089	83.4	1118	13.4	1485	17.8	2227	26.7	2719	32.6
		102	HGO 26 - 102	73.6	1126	15.3	1501	20.4	2252	30.6	2922	39.7
		115	HGO 26 - 115	63.7	1102	17.3	1465	23.0	2198	34.5	2720	42.7
		127	HGO 26 - 127	56.9	1087	19.1	1445	25.4	2168	38.1	2726	47.9
		140	HGO 26 - 140	51.0	1071	21.0	1428	28.0	2142	42.0	2698	52.9
		152	HGO 26 - 152	47.1	1074	22.8	1432	30.4	2148	45.6	2685	57.0
		178	HGO 26 - 178	41.2	1100	26.7	1467	35.6	2200	53.4	2810	68.2
		203	HGO 26 - 203	36.3	1107	30.5	1474	40.6	2211	60.9	2810	77.4
305	HGO 26 - 305	22.6	1035	45.8	1379	61.0	2068	91.5	2554	113.0		
32	16	38	HGO 32 - 038	362.9	2069	5.7	2758	7.6	4137	11.4	4573	12.6
		44	HGO 32 - 044	307.9	2032	6.6	2710	8.8	4064	13.2	4218	13.7
		51	HGO 32 - 051	262.8	2024	7.7	2681	10.2	4021	15.3	4205	16.0
		64	HGO 32 - 064	205.9	1977	9.6	2636	12.8	3953	19.2	4489	21.8
		76	HGO 32 - 076	171.6	1956	11.4	2608	15.2	3912	22.8	4582	26.7
		89	HGO 32 - 089	147.1	1971	13.4	2618	17.8	3928	26.7	4398	29.9
		102	HGO 32 - 102	127.5	1951	15.3	2601	20.4	3902	30.6	4730	37.1
		115	HGO 32 - 115	112.8	1951	17.3	2594	23.0	3892	34.5	4692	41.6
		127	HGO 32 - 127	101.0	1929	19.1	2565	25.4	3848	38.1	4555	45.1
		140	HGO 32 - 140	88.3	1854	21.0	2472	28.0	3709	42.0	4503	51.0
		152	HGO 32 - 152	80.9	1845	22.8	2459	30.4	3689	45.6	4417	54.6
		178	HGO 32 - 178	68.6	1832	26.7	2442	35.6	3663	53.4	4459	65.0
		203	HGO 32 - 203	59.8	1824	30.5	2428	40.6	3642	60.9	4527	75.7
254	HGO 32 - 254	46.9	1787	38.1	2383	50.8	3574	76.2	4484	95.6		
305	HGO 32 - 305	39.2	1795	45.8	2391	61.0	3587	91.5	4626	118.0		
38.5	19.5	51	HGO 38 - 051	313.8	2416	7.7	3201	10.2	4801	15.3	6715	21.4
		64	HGO 38 - 064	230.5	2213	9.6	2950	12.8	4426	19.2	6638	28.8
		76	HGO 38 - 076	196.1	2236	11.4	2981	15.2	4471	22.8	6589	33.6
		89	HGO 38 - 089	171.6	2299	13.4	3054	17.8	4582	26.7	6915	40.3
		102	HGO 38 - 102	142.2	2176	15.3	2901	20.4	4351	30.6	6555	46.1
		115	HGO 38 - 115	124.5	2154	17.3	2864	23.0	4295	34.5	6499	52.2
		127	HGO 38 - 127	112.8	2154	19.1	2865	25.4	4298	38.1	6588	58.4
		140	HGO 38 - 140	103.0	2163	21.0	2884	28.0	4326	42.0	6644	64.5
		152	HGO 38 - 152	93.2	2125	22.8	2833	30.4	4250	45.6	6599	70.8
		178	HGO 38 - 178	80.4	2147	26.7	2862	35.6	4293	53.4	6593	82.0
		203	HGO 38 - 203	70.6	2153	30.5	2866	40.6	4300	60.9	6763	95.8
		254	HGO 38 - 254	56.9	2168	38.1	2891	50.8	4336	76.2	6748	118.6
305	HGO 38 - 305	47.1	2157	45.8	2873	61.0	4310	91.5	6853	145.5		
51	25.5	64	HGO 51 - 064	392.3	3766	9.6	5021	12.8	7532	19.2	8827	22.5
		76	HGO 51 - 076	328.5	3745	11.4	4993	15.2	7490	22.8	8935	27.2
		89	HGO 51 - 089	274.6	3680	13.4	4888	17.8	7332	26.7	8787	32.0
		102	HGO 51 - 102	235.4	3602	15.3	4802	20.4	7203	30.6	8686	36.9
		115	HGO 51 - 115	205.9	3562	17.3	4736	23.0	7104	34.5	8813	42.8
		127	HGO 51 - 127	186.3	3558	19.1	4732	25.4	7098	38.1	8849	47.5
		140	HGO 51 - 140	166.7	3501	21.0	4668	28.0	7001	42.0	9035	54.2
		152	HGO 51 - 152	147.1	3354	22.8	4472	30.4	6708	45.6	8547	58.1
		178	HGO 51 - 178	127.5	3404	26.7	4539	35.6	6809	53.4	8874	69.6
		203	HGO 51 - 203	112.8	3440	30.5	4580	40.6	6870	60.9	9058	80.3
		254	HGO 51 - 254	88.3	3364	38.1	4486	50.8	6728	76.2	8980	101.7
305	HGO 51 - 305	70.6	3233	45.8	4307	61.0	6460	91.5	8747	123.9		

